



TECNOLOGIA S.A.M.
S.A.M. TECHNOLOGY
SMART AUTO MEMORIZATION



ALTA EN EL RECEPTOR
OPERATE ON RECEIVER



FUNCIONAMIENTO DIRECTO
INSTANT OPERATION

| MARCA / BRAND | MODELO / MODEL | TIPOLOGIA / MODE |
|--|---|------------------|
| ACM | TX2, TX2 COLOR, TX4 | |
| ADYX | TE4433H BLUE, 433-HG BRAVO | |
| AERF | COMPACT, HY-DOM, MERCURI B, MERCURI C, SABUTON, MARS, SATURN, ST3/N, TERRA, TMP-1, TMP-2, UNITECH | |
| AERF | MEDVA | |
| ALLMATIC | BROWN, BROWN RED, BRO.OVER, PASS, MINIPASS, TECH3 | |
| ALUTEC | AT-4N-868 | |
| APERIO | GO, GO PRO, GO MINI | |
| APERTO (Sommer) | 4020-TX03-434, TX02-434-2, TX02-868-2 | |
| APRIMATIC | TR, TM4, TXM | |
| ATA | PTX4 BLU, PTX4 PINK | |
| AVIDSEN | 104251, 104250, 104250 OLD, 104250 RED, 104257, 104350, 654250 | |
| BALLAN | FM400, FM400E | |
| BeB PROGET | BUGGY-F, EMY-F2, EMY-F4, ETY-T2, ETY-T4, EMY-C2, EMYC-4, BUGGY-C | |
| <i>Atención: posibles personalizaciones que no se pueden duplicar</i> | | |
| <i>Pay attention possible customizations that cannot be duplicated</i> | | |
| BENINCA | TO. GO. WV, TWV, ROLLKEY, APPLE, LOT WCV, CUPI-DO, TO.GO. QV | |
| BENINCA | IO | |
| BFT | MITTO, MITTO M, MITTO RCB, MITTO A, TRC, GHIBLI, MURALE, KLEIO | |
| CAME | TTS 44 FSK | |
| CAME | TOP 44 RBN, TOP D4 FRN, TOP 44 FGN, TOP 42 FGN | |
| CAME | TW 2 EE, TW 4 EE | |

COMPATIBILIDADES MULTI 2

MULTI 2 COMPATIBILITY



TECNOLOGIA S.A.M.
S.A.M. TECHNOLOGY
SMART AUTO MEMORIZATION



ALTA EN EL RECEPTOR
OPERATE ON RECEIVER



FUNCIONAMIENTO DIRECTO
INSTANT OPERATION

| MARCA / BRAND | MODELO / MODEL | TIPOLOGIA / MODE |
|---|--|------------------|
| CAME | AT 01, AT 02, AT 04 | |
| CAME | TOP D2 RGS, TOP D2 RBS, TOP D2 RKS, TOP D2 RYS, TOP D2 RES, TOP D2 RPS, TOP D4 RGS, TOP D4 RBS, TOP D4 RKS, TOP D4 RYS, TOP D4 RES, TOP D4 RPS | |
| Mando a distancia de doble frecuencia: solo se puede copiar bloqueando la frecuencia del transmisor a 433,92 u 868 MHz <i>Dual frequency remote control: can only be copied by blocking the transmitter frequency at 433.92 or 868 MHz</i> | | |
| CAME | TOP 432 EE, TOP 432 NA, TOP 432 EV | |
| CAME | TOP 434 EE, TOP 434 NA, TOP 434 EV | |
| CARDIN | TRQ S449, TRQ S449 GREEN (PRECODE), TXQ S449, TXQ S449 GREEN, TRQ S486, TXQ S486, S437 TX, XRADO | |
| CARDIN | S504 | |
| CASALI | GENIUS/CASALI A252RC | |
| CHAMBERLAIN LIFT MASTER MOTOR LIFT | 953ESTD, 371 LM, 971 LM, 84330E, 94334CE, 94333E/94334E/94335E, 9747E, 1A5639-7, 1A5477, 1A6487, 132B2372, 94330EML/9333EML/94335EML, 84330EML/84333EML/84335EML, 8747EML | |
| CLEMSA | MUTANCODE, T, T-8, E-CODE N | |
| CLEMSA | MASTERCODE MV | |
| <i>Atención código fijo</i> <i>Warning fixed code</i> | | |
| DASPI | ZERO RC | |
| DEA SYSTEM | PUNTO 278, GOLDR, GENIE R 273, GENIE R-GT2N, MIO TR, GT2M, TRN | |
| DETUMANDO | STANDARD | |
| DITEC | BIXLP, GOL2, GOL4, BIXLG, ZEN 2C, ZEN 4C | |
| DOORHAN | TRANSMITTER 4 | |
| DOORMATIC | MILENY, MILENY-EVO | |

COMPATIBILIDADES MULTI 2

MULTI 2 COMPATIBILITY



TECNOLOGIA S.A.M.
S.A.M. TECHNOLOGY
SMART AUTO MEMORIZATION



ALTA EN EL RECEPTOR
OPERATE ON RECEIVER



FUNZIONAMENTO DIRETTO
INSTANT OPERATION

| MARCA / BRAND | MODELO / MODEL | TIPOLOGIA / MODE |
|---------------|--|------------------|
| ECOSTAR | RSC, RSE, RSZ | |
| EMFA | TE2-433, TE3-433, TE2-868, TE3-868 | |
| ERREKA | IRIS, ROLLER 2, ROLLER 433, ROLLER 868, SOL433, SOL868, VEGA 433, VEGA 868 | |
| FAAC | TML 433SLH, DL 868 SLH, XT 868 SLH, XT 433 SLH, T 868 SLH, T 433 SLH, XT 868 SLH BLACK, XT 433 SLH BLACK | |
| FAAC | XT 433 RC, TE433HG, XT4 433 RCBE | |
| FADINI | JUBI-SMALL, JUBI 433 | |
| GARDENGATE | | |
| GENIE | GITR-3, GIT, GICT390, GIFT390-1, G3T-BX, G1T-BX, GM3T, GICTD, GIFTD | |
| GENIUS | AMIGOLD, AMIGO, KILO, JCL | |
| GENIUS | BRAVO, ECHO | |
| GIBIDI | AU1600, AU1600 WOOD, AU1680, AU1680 WOOD, DOMINO | |
| HÖRMANN | HSE2-868-BS | |
| JCM | NEO, TWIN, KCM, DMIL | |
| JCM | GO, GO PORTIS, GO NORTON, FORSA, EMFA ROPER, TEC | |
| KBLUE | ETH-TEL01 | |
| KEY | 900TXB-42R, TXB 44R, SUB 44R | |
| KING GATES | CLIPPER, STYLO | |
| KLING | KUA, KUA E, KUA S | |
| LABEL | SPYCO | |

COMPATIBILIDADES MULTI 2

MULTI 2 COMPATIBILITY



TECNOLOGIA S.A.M.
S.A.M. TECHNOLOGY
SMART AUTO MEMORIZATION



ALTA EN EL RECEPTOR
OPERATE ON RECEIVER



FUNZIONAMENTO DIRETTO
INSTANT OPERATION

| MARCA / BRAND | MODELO / MODEL | TIPOLOGIA / MODE |
|--|---|------------------|
| LIFE | FIDO | |
| LINEAR | MCT-11, ACT-21, ACT-22, STING RAY ACT-31, STING RAY ACT-34B | |
| MERLIN 2.0 | E945M, E943M, E940M | |
| MERLIN/PROLIFT | C945, C940, C943, M842, M844 | |
| MHOUSE | TX3, TX4, GTX4 | |
| MOOVO | MT4G | |
| NICE | SMILO, FLOR-S, VERY-VR, FLOR-S ERA | |
| NICE | ONE (ON), ON ERA, INTI, ERGO, PLANO, ONE (ON FM) | |
| NORTON | NEO, TXCD | |
| NORTON | GO NORTON, GO MINI NORTON | |
| NOVOFERM | MCHS, MICRO-NOVOTRON 502, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 31, MICRO-NOVOTRON 51, MINI-NOVOTRON 30, MINI-NOVOTRON 50, MNHS | |
| NORMSTAHL | RCV433-2 | |
| O&O | TX, T.COM R4-2, T.COM R8-2, TWIN, TX (NEO), ALFA, TORRES | |
| PECCININ | TX MENBRANA | |
| PRASTEL | MTE, MPSTLE, MPSTP2E, TCE, BFOR, TRQ-P, SLIM-E | |
| PUJOL | TWIN, VARIO, VARIO MARS, VARIO OCEAN, NEO | |
| <i>Atención: posibles personalizaciones que no se pueden duplicar</i> | | |
| <i>Pay attention possible customizations that cannot be duplicated</i> | | |
| RIB | LITHIO | |
| ROPER | NEO | |

COMPATIBILIDADES MULTI 2

MULTI 2 COMPATIBILITY



TECNOLOGIA S.A.M.
S.A.M. TECHNOLOGY
SMART AUTO MEMORIZATION



ALTA EN EL RECEPTOR
OPERATE ON RECEIVER



FUNCIONAMIENTO DIRECTO
INSTANT OPERATION

| MARCA / BRAND | MODELO / MODEL | TIPOLOGIA / MODE |
|---------------|--|------------------|
| ROPER | GO ROPER, GO MINI ROPER | |
| SABUTOM | BROOVER, BROSTAR | |
| SEA | HEAD, SMART DUAL ROLL, SMART-3 ROLLING CODE, COCCINELLA ROLL | |
| SEAV | BE HAPPY RS | |
| SECULUX | NEO | |
| SILVELOX | Mhz 2007, QUARZ SAW | |
| SIMINOR | CVXNL, MITTO | |
| SIMINOR | SIM433 | |
| SOMFY | K-EASY, K-EASY NEW, K-EASY OLD, MITTO, KEY GO RTS, TELIS RTS, KEYTIS RTS, KEYTIS RTS NS, ALARMA | |
| SOMMER | 4010, 4011, 4014 TX03-434-2, 4013 TX03-434-4, 4020 TX03-868-4, 4026 TX03-868-2, 4022 TX02-434-2, 4025 TX02-868-2, 4031 TX08-868-4 | |
| STAGNOLI | KALLISTO, VENUS AV223 | |
| TAU | 250K-SLIMRP, 250K-SLIMR, 250T-4RP | |
| TELCOMA | FM400E, FM400 | |
| TORREC | H101 | |
| TOR LIFT | TORMIT4 | |
| V2 | TSC, TXC, TRC, HANDY, PHOENIX, PHOX 433 | |
| VDS | ECO-R, TRQ P | |